

☐ **GBF1671** Recessed Emergency Shower, Recess Mounted Shower Head

Application: Recessed emergency shower with ceiling mounted recessed shower head. Recessed shower conserves valuable floor space, while eliminating the clutter and obstruction created by conventional shower equipment. Unit can be installed in either a corridor or a lab room, close to where accidents might occur.

ADA Compliance: When installed at recommended mounting heights, unit complies with ADA requirements for accessibility by handicapped persons.

Shower Head: 11-3/4" diameter stainless steel with 20 GPM flow control and flange for flush mounting in ceiling.

Valve: 1" IPS brass stay-open ball valve with stainless steel "panic bar." Pulling bar down activates shower; shower remains in operation until bar is returned to original closed position. Furnished with stainless steel access panel and 1" IPS unions for valve.

Mounting: 16 gauge stainless steel cabinet with flange featuring 3/8" return for recessed mounting in wall.

Supply: 1" NPT female inlet.

Sign: ANSI-compliant identification sign.

U.S. Patent 5,768,721

NOTE: ANSI Z358.1-2014 specifies that shower heads be installed no more than 96" above the finished floor. This unit should therefore not be installed in ceilings over 8 feet. For higher ceiling heights, we recommend either the GBF1670 or GBF1672 showers.

Available Options

_	_					
	ΔP250	-065 Mo	desty cur	tain for	wall mo	unting

- AP280-235 Electric strobe light and alarm horn unit for recess mounting in finished wall. Light illuminates and horn sounds when shower is activated. Includes additional leads for remote monitoring.
- AP280-237 Electric strobe light and alarm horn unit with silencing switch for recess mounting in finished wall. Light illuminates and horn sounds when shower is activated. Includes additional leads for remote monitoring.
- G3800LF Thermostatic mixing valve precisely blends hot and cold water to deliver warm (tepid) water as required by ANSI Z358.1-2014. Refer to "Tempering Valves" section for complete technical and product selection information.



Note: Shown with optional AP280-235 electric light and alarm horn unit (sold separately).


Distributed by: Safety Emporium PO Box 1003 Blackwood, NJ 08012 Ph: (866) 326-5412 toll-free Fax: (856) 553-6154 esupport@safetyemporium.com www.safetyemporium.com







GBF1671 Recessed Emergency Shower, Recess Mounted Shower Head



- 2. STANDARD DIMENSION FROM SHOWER HEAD TO WALL IS 24"
- (610mm). WHEN UNIT IS USED IN BARRIER-FREE APPLICATIONS, DIMENSION SHOULD BE 36" (915mm).
- CABINET IS 16 GAUGE TYPE 304 STAINLESS STEEL WITH #4 BRUSHED SATIN FINISH.
- 4. PROVIDE 7 1/4" (184mm) X 14 1/2" (368mm) CUTOUT IN WALL FOR HOUSING INSTALLATION.
- 5. TRIM PIECE MUST BE FRAMED IN THE WALL.

THIS SPACE FOR ARCHITECT/ENGINEER APPROVAL

Due to continuing product improvement, the information contained in this document rev. 021920 is subject to change without notice. All dimensions are ± 1/4" (6mm).

Distributed by: Safety Emporium PO Box 1003 Blackwood, NJ 08012 Ph: (866) 326-5412 toll-free Fax: (856) 553-6154 esupport@safetyemporium.com www.safetyemporium.com







312 447 8100 TELEPHONE 312 447 8101 FACSIMILE gesafety.com



