



# Large Volume Stirrers

Distributed by:  
Safety Emporium  
PO Box 1003  
Blackwood, NJ 08012  
Ph: (866) 326-5412 toll-free  
Fax: (856) 553-6154  
esupport@safetyemporium.com  
www.safetyemporium.com



## **Powerful Motor and Magnet Mixes Samples Up To 200 L**

OHAUS offers four models for stirring capacities between 25 to 200 L, allowing you to choose the right model for your application. The broad top plate surface allows processing of oversized vessels such as carboys for your large volume stirring. The powerful magnetic drive is also capable of mixing highly viscous materials.

### **Unique Features Include:**

- High Volume Stirrers (STLC1DG and STLC2DG) with a 100 or 200 L capacity are made with a stainless steel base offering durability and stability, and feature a 54 x 63 cm stainless steel top plate.
- High Volume Stirrers (STHVAL and STHVDG) have a large 32 x 28 cm top plate that is chemical-resistant with a white reflective surface that is easy to clean. Digital and non-digital models allow you to choose the right model for your application.
- Speed ramping feature slowly increases the motor speed for improved safety and enhanced coupling. Avoids splashing, improves spin bar control and provides excellent low-end speed control.

# Large Volume Stirrers

Model	STHVAL	STHVDG	STLC1DG	STLC2DG
Control	Analog		Digital	
Speed Range	60 rpm to 1400 rpm		100 rpm to 1800 rpm	100 rpm to 1650 rpm
Timer	N/A		1 second to 160 hours	
Capacity	25 L		100 L	200 L
Plate Construction	Glass Filled Nylon		Stainless Steel	
Dimensions (H x L x W)	4 x 17 x 11 in. / 10.2 x 43.2 x 27.9 cm		5.25 x 28.5 x 26.75 in. / 13.3 x 72.4 x 68 cm	
Plate Dimensions (L x W)	12.5 x 11 in. / 31.8 x 27.9 cm		21.25 x 25 in. / 54 x 63.5 cm	
Net Weight	13.6 lb / 6.2 kg		63.5 lb / 28.8 kg	
Power	120 V, 50/60 Hz		120 V, 50/60 Hz	
Power Consumption	75 W		90 W	
Working Environment	41 °F – 104 °F, 80% RH*, non-condensing / 5 °C – 40 °C, 80% RH*, non-condensing			

\*RH = Relative Humidity

## Other Standard Features & Equipment

High Volume Stirrers feature a cast aluminum housing and glass filled nylon top plate. Large Capacity Stirrers feature a stainless steel top plate and aluminium housing. Models include either a 70 mm egg shaped stir bar (STHVAL, STHVDG, STLC1DG) or 102 mm stir bar with pivot ring (STLC2DG). Speed ramping feature slowly increases motor speed for enhanced coupling and improved stirring. Microprocessor-controlled for precise speed regulation. Timer counts up or when programmed to a set time, will turn off stirring and sound alarm when timer reaches zero.

## Compliance

- Product Safety: CAN/CSA C22.2 No. 61010-1, CAN/CSA C22.2 No. 61010-2-051, UL 61010-1
- Electromagnetic Compatibility: ICES-003 Class A, FCC Part 15 Class A
- Compliance Marks: UL (for STHVAL and STHVDG) and TUV (for STLC1DG and STLC2DG)

Distributed by:  
**Safety Emporium**  
 PO Box 1003  
 Blackwood, NJ 08012  
 Ph: (866) 326-5412 toll-free  
 Fax: (856) 553-6154  
[esupport@safetyemporium.com](mailto:esupport@safetyemporium.com)  
[www.safetyemporium.com](http://www.safetyemporium.com)

## Accessories


- Spinbar, 7 cm, PTFE\* .....30400149
- Spinbar, 10 cm with Pivot Ring, PTFE\*\*.....30400150

\*Included with STHVAL, STHVDG, STLC1DG


\*\*Included with STLC2DG

## Dimensional Drawings


STHVAL




STHVDG



STLC1DG



STLC2DG



80776575\_G 20200609 © Copyright OHAUS Corporation

**OHAUS CORPORATION**  
 \* 7 Campus Drive  
 Suite 310  
 Parsippany, NJ 07054 USA  
 Tel: 800.672.7722  
 973.377.9000  
 Fax: 973.944.7177

[www.ohaus.com](http://www.ohaus.com)  
 With offices throughout  
 Europe, Asia and  
 Latin America

\*ISO 9001:2015  
 Registered Quality  
 Management System

